




Dimensions



Name	NANO RECESSED FLOOD 3500K N
Reference	A5390113N
Colour	Black
RAL	Colour in the mass looks alike RAL 9005
Category	CEILING RECESSED

PRODUCT

Type	LED
Gross luminous flux	625 lm
Colour temperature	3500 K
Chromatic stability	MacAdam Step 2
Colour Rendering Index	CRI>90
Power	5,5 W
Current	250 mA
Efficacy	114 lm/W
LED lifespan	L80B10 >55.000h
Energy efficiency class	E

LIGHT SOURCE

Lighting efficiency	84%
Light beam angle	34°

LIGHTING FIXTURE | PHOTOMETRIC DATA

Driver	Included - Connected
Power values of the system	7,04 W
Frequency	50/60 Hz
Dimming	No Dim - Other DIM, please consult
Electrical insulation class	□

LIGHTING FIXTURE | ELECTRICAL DATA


Sealing	IP20
Emergency power supply	Please Consult
Recess measurements	Ø30 mm
Weight	75 g
Packaged weight	105 g
Packaging dimensions	155 x 60 x 45 mm
Units per package	1
Materials	Aluminium / Acrylonitrile Butadiene Styrene / Polycarbonate

OTHER DATA




Nano is an exercise in formal synthesis that redraws the boundaries of technical lighting, offering maximum light output with minimum use of raw materials. Nano is an evolution of the downlight because of its basic and compact design. It provides up to 640 lumens from a compact body.

Polar diagram



Conical diagram



UGR

Glare Evaluation According to UGR												
ρ Ceiling		70	70	50	50	30	70	70	50	50	30	30
ρ Walls		50	30	50	30	30	50	30	50	30	30	30
ρ Floor		20	20	20	20	20	20	20	20	20	20	20
Room Size X Y		Viewing direction at right angles to lamp axis					Viewing direction parallel to lamp axis					
2H	2H	1.0	1.6	1.2	1.8	2.0	0.9	1.6	1.2	1.8	2.0	
	3H	3.1	3.7	3.4	3.9	4.1	3.2	3.8	3.5	4.0	4.2	
	4H	4.3	4.9	4.6	5.1	5.4	4.4	4.9	4.7	5.2	5.4	
	6H	5.5	6.1	5.9	6.3	6.6	5.6	6.1	5.9	6.4	6.7	
	8H	6.1	6.6	6.4	6.9	7.2	6.2	6.7	6.5	6.9	7.2	
4H	12H	6.8	7.3	7.1	7.6	7.9	6.9	7.3	7.2	7.6	8.0	
	2H	1.6	2.2	1.9	2.4	2.7	1.6	2.2	1.9	2.4	2.7	
	3H	4.0	4.5	4.4	4.8	5.1	4.1	4.6	4.5	4.9	5.2	
	4H	5.5	5.9	5.9	6.2	6.6	5.5	5.9	5.9	6.2	6.6	
	6H	6.9	7.3	7.3	7.6	8.0	6.9	7.3	7.3	7.6	8.0	
8H	8H	7.6	7.9	8.0	8.2	8.6	7.6	7.9	8.0	8.3	8.7	
	12H	8.4	8.7	8.8	9.1	9.5	8.5	8.7	8.9	9.1	9.5	
	4H	6.0	6.3	6.4	6.7	7.1	6.0	6.3	6.4	6.7	7.1	
	6H	7.7	7.9	8.1	8.3	8.8	7.7	7.9	8.1	8.3	8.7	
	8H	8.5	8.7	8.9	9.1	9.6	8.5	8.7	9.0	9.2	9.6	
12H	12H	9.5	9.7	10.0	10.1	10.6	9.6	9.7	10.1	10.2	10.7	
	4H	6.1	6.4	6.6	6.8	7.2	6.1	6.4	6.6	6.8	7.2	
	6H	7.9	8.1	8.4	8.5	9.0	7.9	8.0	8.3	8.5	9.0	
	8H	8.8	8.9	9.3	9.4	9.9	8.8	9.0	9.3	9.4	9.9	
Variation of the observer position for the luminaire distances S												
S = 1.0H S = 1.5H S = 2.0H		+2.7 / -0.9 +4.8 / -1.2 +6.6 / -1.6					+2.4 / -0.7 +4.4 / -1.0 +6.1 / -1.3					
Standard table Correction Summand		BK05 -7.1					---					
Corrected Glare Indices referring to 625lm Total Luminous Flux												



Fuente de luz (LED) reemplazable por un profesional autorizado

Replaceable (LED only) light source by an authorized professional.

Source lumineuse (LED) remplaçable par un professionnel agréé

Sorgente luminosa (LED) sostituibile da parte di un professionista autorizzato

Austauschbare (LED) Lichtquelle durch einen autorisierten Fachmann



Equipo de control reemplazable por un profesional autorizado

Replaceable control gear by an authorized professional

Dispositif de commande remplaçable par un professionnel agréé

Alimentatore sostituibile da parte di un professionista autorizzato

Auswechselbares Betriebsgerät durch autorisierten Fachmann

Instrucciones para el final de vida y la eliminación de los componentes:

Instructions on end-of-life and component disposal:

Instructions pour la gestion des composants en fin de vie et leur mise au rebut :

Istruzioni per il fine vita e lo smaltimento dei componenti:

Anweisungen zur entsorgung der Leuchtenkomponenten:



Interrumpir la alimentación del aparato
Cut the power supply to the luminaire
Couper l'alimentation du luminaire
Interrompere l'alimentazione dell'apparecchio
Stromversorgung der Leuchte unterbrechen



Quitar la(s) fuente(s) de luz para el desecho
Remove light source(s) for disposal
Retirer la (les) source(s) lumineuse(s) pour l'élimination
Rimuovere la/le sorgente/e di luce per lo smaltimento
Lichtquelle(n) zur Entsorgung entfernen



Quitar la batería para el desecho
Remove the battery for decommissioning
Retirer la batterie pour sa mise au rebut
Rimuovere la batteria per la dismissione
Die Batterie ordnungsgemäß entsorgen



Quitar el equipo de control para el desecho
Remove control gear for disposal
Retirer le dispositif de commande pour l'élimination
Rimuovere l'alimentatore per lo smaltimento
Betriebsgerät zur Entsorgung ausbauen

Enviar los materiales a un centro de recogida RAEE
Send the materials to a WEEE collection centre
Envoyer les matériaux dans une déchetterie DEEE
Inviare i materiali ad un centro di raccolta RAEE
Die Materialien in einem WEEE-Zentrum entsorgen

